







Legend	
	Halogen Red Strobe Light
	Xenon Red Beacon Light
	Acoustic Siren, >100 db
	Oxigraf 4-port O2iM Oxygen Deficiency Monitor (installed at height 1.7 m FFL)
	Oxigraf 1-port O2iM Oxygen Deficiency Monitor (installed at height 1.7 m FFL)
	ODH Monitoring System Distributed I/O Enclosure (double-door, W: 600 mm, D: 1000 mm, H: 2000 mm)

G04-Field Devices-ODH Monitors




Legend	
	Halogen Red Strobe Light
	Xenon Red Beacon Light
	Acoustic Siren, >100 db
	Oxigraf 4-port O2IM Oxygen Deficiency Monitor (installed at height 1.7 m FFL)
	Oxigraf 1-port O2IM Oxygen Deficiency Monitor (installed at height 1.7 m FFL)
	ODH Monitoring System Distributed I/O Enclosure (double-door, W: 600 mm, D: 1000 mm, H: 2000 mm)

G04-Field Devices-Lights & Sounders

Legend	
	Halogen Red Strobe Light
	Xenon Red Beacon Light
	Acoustic Siren, > 100 db
	Oxigraf 4-port O2iM Oxygen Deficiency Monitor (installed at height 1.7 m FFL)
	Oxigraf 1-port O2iM Oxygen Deficiency Monitor (installed at height 1.7 m FFL)
	ODH Monitoring System Distributed I/O Enclosure (double-door, W: 600 mm, D: 1000 mm, H: 2000 mm)

CXB-CXH:ODH-RIO-2




O2iM-13




Coldbox Hall
G02.100.2002

O2iM-17



O2iM-16



O2iM-19



O2iM-18









O2iM-15




O2iM-14



CXB-Field Devices-ODH Monitors

Legend	
	Halogen Red Strobe Light
	Xenon Red Beacon Light
	Acoustic Siren, >100 db
	Oxigraf 4-port O2IM Oxygen Deficiency Monitor (installed at height 1.7 m FFL)
	Oxigraf 1-port O2IM Oxygen Deficiency Monitor (installed at height 1.7 m FFL)
	ODH Monitoring System Distributed I/O Enclosure (double-door, W: 600 mm, D: 1000 mm, H: 2000 mm)


CXB-CXH:ODH-RIO-2






Coldbox Hall
G02.100.2002


CXB-Field Devices-Lights & Sounders

CTL confined space
G04.090.7002



Legend	
	Oxigraf 1-port O2iM Oxygen Deficiency Monitor (installed at height 1.7 m FFL)
	Xenon Red Beacon Light
	Acoustic Siren, >100 db

CTL-Field Devices-ODH Monitors

 EUROPEAN SPALLATION SOURCE <small>Documentation production 2017-02-05</small>	DRAWN BY: MM & ATD CHECKED BY: MM APPROVED BY: SLD DATE: 01/09/2017 PROJECT: ESS	DATE: 2017-09-01 NAME: ACCELERATOR PROJECT: CTLG-Devices-Distribution map FUNCTION:	DRAWING TITLE: Accelerator ODH Detection System DRAWING NUMBER: ESS-0089356 LAYOUT: Preliminary SHEET: =ESS.ACC.F02&LD/7 UNIT: &PD/1	ESS-0089356 PRELIMINARY A1 100
	PROJECT: CTLG-Devices-Distribution map FUNCTION:			PRELIMINARY A1 100